



## Hach 934-AH Filters, 70 mm, 100/pk

**Nr. produs:** 2511209

RON Preț (fără TVA): Contact

Nu este afișată data expirării

Hach 934-AH Filters are specified for use in Standard methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5  $\mu\text{m}$  particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500 °C, which is a unique and especially important feature for laboratories performing Fixed and Volatile Suspended Solids analysis of water and wastewater.

The trademark 934-AH is owned by GE Healthcare/Whatman Inc. and used under exclusive license for purposes of private label.

---

### Specificații

Cantitate:	100 /pk
Diametru:	70 mm
Dimensiune por:	1.5 $\mu\text{m}$
Material:	Glass Microfiber
Unitate:	100/pk